

# HEMOMATIK Sweden

Liquid level switch

Art.nr. HM40-S

IP67

Drawing nr. HM40-S

Rev. 1

Approved P.L 000413


Scale 1:1

Date 000309

Sign. MEM

Rev. date 000413

brown  
blue



When using this space for mounting bracket, please make sure not to use bracket thicker than 1,5mm. Use only non magnetic material.

Make sure that the o-ring is centered and pressing around the cable before tightening the nut.

■ = Switch closed

□ = Switch open

Contact rating *	20 VA
max voltage	50 V
max current	1 A

\* = resistive load